


CLS₁ – CRYO LINEAR SCANNER 1



Features

- xy and z model, xyz configurable
- Non-magnetic
- Flexure mechanism
- Robust: easy handling and high load capacity
- High driving stiffness
- Open aperture
- 20 mK to 375K, vacuum compatible
- Bipolar driving voltage in cryo to increase stroke
- Dynamic operation

Description / Applications

The CLS₁ is the smallest model in the CLS series. A non-magnetic linear scanner series for all-round fine positioning applications in a cryo-vacuum. Special attention is given to realize a robust and rigid mechanism that can tolerate significant handling and payload forces. The central open aperture allows the transfer of fibers, wires, or light through the scanner body. The xy-scanner can be combined with the z-scanner for motion along all 3 linear axes.

Specifications

General info		
Type of motion	Scanning, xy and z, configurable to xyz	
Dimensions	See drawings below	
Operational environmental conditions	20 mK to 375 K, ambient to UHV	
Weight	xy 15 g	z 10 g
Scanning motion		
Scanning range @ 300 K	xy 30 x 30 micron	z 27 micron
Scanning range @ 4 K	xy 14 x 14 micron	z 13 micron
Minimal step size	Sub-nm	
Drive voltage @ 300 K	-30 V to 120 V	
Drive voltage @ 4 K	-150 V to 150 V	
No load resonance frequency	xy 600 Hz	z 400 Hz
Forces and load capacity		
Load capacity	5 N all directions	
Materials		
Main body	Titanium	
Piezo actuator	Low voltage multilayer, ceramic insulated	
Model specific information		
-V, -HV or -UHV	Level of vacuum compatibility, see the glossary on the homepage for details	
Electronics CPSC		
Controller Base Cabinet	CAB	
Driver for stepping and scanning	CADM or PSM	

Ordering Information

Available Models

CLS1-XY-V	Cryo Linear Scanner 1-XY
CLS1-Z-V	Cryo Linear Scanner 1-Z

Available Options

-HV	Upgrade to High Vacuum compatibility
-UHV	Upgrade to Ultra High Vacuum compatibility

Accessories

I1-CLS1	Interface plate to mount CLS1-XY or CLS1-Z on CBS10 positioner
AKM1	Accessory Kit Mechanical 1
AKE1	Accessory Kit Electrical 1


Mechanical and electrical information



Download 3D step files and manuals from:
<https://www.jpe-innovations.com/cryo-nano-products/>

Contact

For quotations, specials, or engineering services, please contact us at:
<https://www.jpe-innovations.com/contact/>

Drawings





PROJ	SCALE	PART NAME	PART NUMBER
2122-001-26	3:1	CLS1-Z	A001395
MP1		Aziëlaan 12, 6594AG Maastricht-Airport NL	A3 SHEET 1 OF 1

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of JPE. JPE disclaims any liability with regard to the accuracy, completeness, and timeliness of the information provided.

STATUS: RELEASED